

Versa**TREK**[®]

Instrument Specifications

528 Model

Height.....	76 1/4 in.; 194 cm
Width.....	52 in.; 132 cm
Depth.....	30 3/4 in.; 78 cm
Weight (without bottles).....	1,212 lbs; 561 kg
Distributed load* (528-22 with bottles).....	132 lbs/ft ² ; 644 kg/m ²
Heat emission.....	2,307 BTU/hr



240 Model

Height.....	40 1/4 in.; 103 cm
Width.....	52 in.; 132 cm
Depth.....	30 3/4 in.; 78 cm
Weight.....	656 lbs; 304 kg
Distributed load* (240-10; with bottles).....	70 lbs/ft ² ; 339 kg/m ²
Distributed load* (240-10; without bottles).....	59 lbs/ft ² ; 290 kg/m ²
Heat emission.....	1,495 BTU/hr

240 Model with Cart

Height.....	40 1/4 in.; 103 cm
Height (on cart).....	76 in.; 193 cm
Width.....	52 in.; 132 cm
Depth.....	30 3/4 in.; 78 cm
Weight (with cart, without bottles).....	1,201 lbs; 545 kg
Distributed load* (240-10 cart with bottles).....	119 lbs/ft ² ; 580 kg/m ²
Distributed load* (240-10 cart without bottles).....	109 lbs/ft ² ; 531 kg/m ²
Heat emission.....	1495 BTU/hr
VersaTREK 240 Cart.....	Product # 6020-30



*Distributed load refers to the force that the unit exerts across its "foot print" (width x depth), measured in pound-force per square foot (kilogram-force per square meter).

VersaTREK[®]

Clearance requirements (240 and 528 models)

Front.....	48 in.; 122 cm
Rear.....	4 in.; 11 cm
Top.....	24 in.; 61 cm
Side.....	4 in.; 11 cm

Environmental (240 and 528 models)

Operating temperature.....	59° F to 82° F; 15° C to 28° C
Humidity (non-condensing).....	10% to 90%
Operating elevation (maximum).....	9842 feet; 3000 meters

Electrical

240 Unit

Line Voltage.....	110/240 vAC +/- 10%
Line Frequency.....	50/60 Hz +/- 5%
Wattage.....	700 watts (typical)

528 Unit

Line Voltage.....	110/240 vAC +/- 10%
Line Frequency.....	50/60 Hz +/- 5%
Wattage.....	1200 watts (typical)

Certifications (240 and 528 models)

UL.....	3101-1
CSA.....	22.2 No. 1010.1
IEC.....	61010-1:90 + A1:92 + A2:95
IEC.....	61326-1, 2002

VersaTREK Windows[®] Software

VersaTREK Computer Package*.....	6110-31
----------------------------------	---------

* The VersaTREK Computer Package includes 15" Touch Screen Monitor, Microsoft Access XP, VersaTREK Windows Software CD, HP Laserjet Printer, UPS 1200 VA Universal 6-Outlet, and VersaTREK Operator's CD Manual.

VersaTREK Accessories

VersaTREK Myco Adaptors, 25/box.....	6040-30	Thermometer, 18°C - 50°C, 135mm, each*.....	6440-30
Red Disable Location Cap, each*.....	6044-30	Absorbent Sheet, each*.....	6444-30
VersaTREK Stylus, 4/pack*.....	6420-30	Label, Drawer, Numbered 1 - 22, each*.....	6452-30
VersaTREK Stylus Holder, each.....	6422-30	VersaTREK EZ-ID Labels, 100/pack.....	6450-35
Bottle Carry Rack, 24-positions*.....	6424-30	VersaTREK Connectors, 50/box.....	7150-44

* These items are included in the VersaTREK Starter Kit (6499-31). Quantity of items in the Starter Kit are: 5 red disable location caps, 1 VersaTREK stylus 4-pack, 1 bottle carry rack, thermometer, 3 absorbent sheets, 1 set of drawer labels. One cable, CAT5E 25' Snagless Patch (6172-30), is also included with the Starter Kit. One complete Starter Kit is shipped with each VersaTREK instrument.

Bottle Capacity — 240 Model

Configuration	Number of Drawers	Maximum Annual Bottle Volume — 5 Day Blood Culture	Maximum Annual Bottle Volume — 7 Day Blood Culture	Maximum Annual Bottle Volume — Myco	Product Number
96	4	7,000	5,000	850	6240-04
144	6	10,500	7,500	1,250	6240-06
192	8	14,000	10,000	1,700	6240-08
240	10	17,500	12,500	2,100	6240-10

Bottle Capacity — 528 Model

336	14	24,500	17,500	3,000	6528-14
384	16	28,000	20,000	3,500	6528-16
432	18	31,500	22,500	3,800	6528-18
480	20	35,000	25,000	4,300	6528-20
528	22	38,500	27,500	4,700	6528-22

